

C-434 Heavy Residential Wall Hydrant









- **Anti-Siphon**
- **Double Check Valve**

With Integral P-004 Vaccum Breaker


PRIER C-434 provides a year round source of water in areas that are subject to freezing temperatures. The hydrant valve is connected to the supply piping in the heated portion of the structure, eliminating the possibility of freezing. To assure freeze protection, the hydrant will drain even with the hose attached and under pressure without spray back.

The C-434 combines freezeless hydrant features with self-draining, anti-siphon and two backflow check valves. The vacuum breaker/ backflow preventer provides protection against cross-connection of the potable water supply, while venting to eliminate any vacuum. Upon closure, valve drains even with closed end hose attached. No special installation tools are required.

FEATURES

- Double check valve and anti-siphon vacuum breaker
- Drains automatically with hose attached
- Integral cast flange with built-in drainage pitch
- Solid brass body
- Per ASSE 1052, pressure rated to 125 PSI, temperature to 140° F
- Satin nickel plated body maintains attractive finish
- Soft-grip coated cast aluminum handle
- Metal collar covers drainage holes and protects against insect nesting while closing under pressure
- Cycle tested to simulate 5000 turns
- Patent protected
- Each valve air-tested at factory for leak-free quality

ORDERING



INLET STYLES



D Style 1/2" MPT x 1/2" SWT





T Style 3/4" MPT x 1/2" FPT



W Style ½" Wirsbo® PEX



3/4" SWT




3/4" Crimp PEX




1/2" Press-Fit




C-434 REPLACEMENT PARTS






| ID | Part No. | Description | |
|----|-------------------------------------|------------------------------------------------|--|
| 1 | See Replacement Stems Section | Stem Assembly, Contains: 1, 5 | |
| 2 | P-164KT-805 | Operating Handle and Screw Kit | |
| 3 | 324-1003 | Washer Packing | |
| 4 | C-434KT-906 | Vacuum Breaker Repair Kit* | |
| 5 | C-434KT-902 | Stopper and Pin Kit (with tool and o-ring) | |
| 6 | 300-6003 | Valve Stem Cap | |
| 7 | C-434KT-804 | Loose Key Conversion Kit to C-534 | |
| | C-434KT-907 | Overhaul Kit for C-434 Contains: 2, 3, 4, 5 | |

*When assembling the vacuum breaker, ensure the dome is facing out on the check spider and the bottom is facing out on the silicone washer.





REPLACEMENT STEMS

Hydrant Length-



| Part No. | Stem Length | Description |
|------------|--------------------------------------|--------------------------------------------|
| P-231-04CC | 4 ⁷ / ₈ " OAL | Close Coupled Stem for C-434/C-534 Hydrant |
| P-231-0404 | 6 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0406 | 8 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0408 | 10 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0410 | 12 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0412 | 14 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0414 | 16 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0416 | 18 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0418 | 20 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0420 | 22 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0422 | 24 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |
| P-231-0424 | 26 ¹ / ₂ " OAL | Stem for C-434/C-534 Hydrant |

^{**}For stems manufactured before 2013, see C-434 Series retired style spec sheet at PRIER.com.